

# sensoryco.

see. feel. smell. real.

## SmX-4DS

for Targeted 4D & Simulator FX

SensoryCo's SmX-4DS aroma system provides a method of placing smells directly in a target area instantaneously. With the capability of delivering up to 3 simultaneous aromas per Chamber Module, we provide a platform to integrate to outside controls to launch scents based on simulator content.

Individual aromas are chambered and released upon relay contact closure. All you need to do is trigger the relay contact closure at the instant that you want to introduce smell and we handle the rest.

The system uses dry aroma delivery versus atomized oils that fall out and deposit or cause damage to electrical components. Aroma media is contained in SensoryCo SOCs and easily changed out when depleted or content changes.

The SensoryCo SmX-4D system uses our proprietary nozzle design and low profile plumbing that allows for a clean integration to a variety of physical environments, structures or seats.

### Specifications


Aroma Capacity:	Up to 3 simultaneous aromas per Chamber Module
Aroma Consumption:	200 hours continuous (*average depends on conditions)
Key Features:	Easy integration Targeted release Compressed air canister or air compressor delivery
Media:	High Intensity Infused Pearl Bead Socs
Delivery:	Dry aroma delivery, no atomized oils
SmX-4D Controller Dimensions:	20" h x 18" w x 8" d 508 mm h x 457 mm w x 203 mm d
Chamber Module Dimensions:	28" h x 20" w x 8" d 711 mm h x 508 mm w x 203 mm d
Input Power:	120 VAC
Power Consumption:	120 Watts
Control:	Relay contact closure
Warranty:	1 Year, Unlimited Customer Support
Origin:	Made in U.S.A.



SmX-4D aroma ports



SmX-4DS Chamber Module



www.smellreal.com